

EuroDesign

Wood Engineering


EUDE NAUTIC – TOILET LID – ASSEMBLING INSTRUCTIONS



Pre-drill the screw holes.



Fill the drilled holes with a good quality sealant.



Insert a screw to a depth between 12 and 14 mm into the lid.

Note :

We do not recommend varnishing the product.

TOOLS



Stainless Steel, Wood Screws




Drill



Screw Driver



Sealant



EUDE
eurodesign.se

EuroDesign Scandinavia AB
Rävebergsvägen 120B, SE-424 67, Angered, Sweden

PT EUDE Indonesia
Jl. Industri Terboyo Timur D-35, Semarang, 50118, Indonesia

sales@eurodesign.se
www.eurodesign.se